AMG SERIES



BOLT IN AUTOMOTIVE FUSES

SPECIFICATIONS:

Applications: For high current applications. Use with Bussmann HMG or FMG fuseholders. (See pages 12-13.)
Current Rating: 100-300A.
Voltage Rating: 32VDC.*
Interrupt Rating: 1,000A @ 32VDC.
Housing Material: UL-Rated 94V-0 thermoplastic.
Terminal Material: Copper.
Mounting: M8 or 5/16-18 or less studs on 2.00 in (50.8mm) centers.
Marking: Color-coded amperage ratings.

*Consult factory for higher voltage fuses.

TIME-CURRENT SPECIFICATIONS

% of Rating	Opening Time	
	Minimum	Maximum
100	100 hrs	
135	120 s	1800 s
200	1 s	30 s
350	0.1 s	5 s
600	0.02 s	1 s


PART NUMBERING SYSTEM


Series **Rating**

B K / A M G — ❑❑❑

100 – 100 amps
125 – 125 amps
150 – 150 amps
175 – 175 amps
200 – 200 amps
225 – 225 amps
250 – 250 amps
300 – 300 amps

DIMENSIONS (Dims. are shown for reference only. Consult factory for latest prints)





Downloaded from Arrow.com.