

MPT-2C2C240045M-NN



MPOptimate® Trunk Cable, polarity A, 24 fiber dual row, OFNP 3.8 mm, OM4, 45 m, no breakout

OBSOLETE

This product was discontinued on: July 29, 2019

Product Classification

Regional Availability	Latin America North America
Portfolio	NETCONNECT®
Product Type	Fiber trunk cable assembly
Product Brand	MPOptimate®
Product Series	MPT

General Specifications

Color, boot A	Black
Color, boot B	Black
Color, connector A	Aqua
Color, connector B	Beige
Connector A, quantity	2
Connector B, quantity	2
Interface, Connector A	MPO-24/UPC Female
Interface Feature, connector A	24-Fiber Unpinned
Interface, Connector B	MPO-24/UPC Female
Interface Feature, connector B	24-Fiber Unpinned
Jacket Color	Aqua
Total Fibers, quantity	48

Dimensions

MPT-2C2C240045M-NN

Cord Length 45 m | 147.638 ft

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

