


RoHS
Compliant

VERSION	DESCRIPTION	DATE
1.0	New Release	2018/4/12



PART NO	DRAWING NO	CABLE LENGTH "L"	COLOR
913M-2-3-00100-G	671-451-A	1000±100	aqua
913M-2-3-00200-G	671-451-B	2000±100	aqua
913M-2-3-00300-G	671-451-C	3000±100	aqua
913M-2-3-00500-G	671-451-D	5000±100	aqua
913M-2-3-00700-G	671-451-E	7000±100	aqua
913M-2-3-01000-G	671-451-F	10000±100	aqua
913M-2-3-01500-G	671-451-G	15000±100	aqua
913M-2-3-02000-G	671-451-H	20000±100	aqua
913M-2-3-02500-G	671-451-I	25000±100	aqua

NOTES:

Insertion loss < 0.3 dB

6	Dust Cover
5	Shrinkage Tube
4	1/2 Code
3	ST MM Connector (Metal housing Red/black boot)
2	LC MM Duplex Connector (Beige housing White boot)
1	2.0mm,Duplex,MM-50/125 OM3, PVC, Optical Fiber Cable(Aqua)
No.	Description

CnC Tech, LLC Industrial Cable and Connector Technology					
		TITLE	Patch Cord, LC-ST,MM-50/125 OM3, Duplex, PVC, aqua, 2.0mm, xxM		
UNIT	mm	P/N	DRAWN BY		
unless otherwise stated Tolerances mm XXX.XX±0.3 XX.XX ±0.2 X.XX ±0.1		Customer P/N	913M-2-3-0xxxx-G	CHECK BY	
SIZE	A4	SCALE	Free	PAGE	1/1
		APPROVAL BY			