Part Number : 643191216
Product Description : .635mm, 1.50mm, CMC Receptacle, 32 Circuits, Left Wire Output, Blue Coding, Mat Sealed
Series Number : 64319
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

643191216_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-64319-002-001.pdf

AS-64319-002-CH-001.pdf

AS-64319-002-FR-001.pdf

AS-64319-002-SP-001.pdf

984200002-AS-KR-000.pdf

AS-98420-002-001.pdf

AS-98420-002-CH-001.pdf

AS-98420-002-FR-001.pdf

AS-98420-002-SP-001.pdf

PK-64319-001-001.pdf

PS-64319-001-001.pdf

PS-64319-002-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC

Downloaded from Arrow.com.

Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	64319
Description	.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Left Wire Output, Blue Coding, Mat Sealed
Application	Automotive, Wire-to-Board
Comments	Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C; Current max = 6.0A for 0.635mm Terminal (0.75mm^2 wire) and 12.0A for 1.50mm Terminal (2.00mm^2 wire)

Downloaded from Arrow.com.

Component Type	Receptacle
More Detailed Tech Information	Sealed, high-density, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Product Name	CMC
UPC	883906129743

Physical

Circuits Detail	8 x 1.5mm & 24 x 0.635mm terminals
Circuits (maximum)	32
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	29.426/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.70mm
Polarized to Mating Part	Yes
Sealed	Sealed
Stackable	No
Temperature Range - Operating	-40° to +125°C
Terminal Size	0.635, 1.5

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Downloaded from Arrow.com.

Description	Part Number
Mates With	Please contact Molex for details

Use with Part(s)

Description	Part Number
CMC Wire Cap for 32 Circuits, CMC Receptacle Mat Sealed	643191201
CMC 0.635mm Blind Cavity Plug	643251010
CMC 1.50mm Blind Cavity Plug	643251023
0.635mm CMC CP Female Terminals	64322
1.50mm CMC CP Female Terminals	64323

Application Tooling

Global

Description	Part Number
Continuity Test Pen Assembly	638121100
Unlocking Tool for CMC and CMX Receptacle Connector	638241200

Downloaded from Arrow.com.