

Rating	3A. 125VAC, 1.5A. 250VAC
Contact Resistance	50m ohm max.
Insulation Resistance	DC 500V 100M ohm min.
Dielectric Strength	AC 1000V 1 minute

Mounting Hole



Circuit Diagram




SPST OFF - (ON)

( )= Momentary

Cut-Out 4mm thk. max.

BASE COLOR: Black

BUTTON COLOR: Red



Order Chart

Series		Terminal			
GPB024	A	05	B	R	Button Color
	Function		Base Color		

RoHS Compliant

MASTER

1	Removed Logo & Added Order Chart. DW 1/05/23.			

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 12/25/09	Rev. 1	Unit: mm	Checked By: G. GULD

Title: PUSH BUTTON SWITCH

CW P/N: GPB024A05BR

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Downloaded from Arrow.com.