USB-C to USB-B Cable - USB 2.0, (M/M), 6 ft. (1.83 m)

MODEL NUMBER: **U040-006**



Connect devices with a USB Type-B connector to the USB Type-C (USB-C) port on your tablet, laptop, ultrabook or computer

Features

- 6-ft. USB 2.0 Type B to Type C (USB-C) device cable
- USB Type C connector is reversible, so there is no guessing on which way to plug it in.....it connects in either direction!
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair / 22AWG Power Pair; Supports 1.5A current

Highlights

- 6-ft. USB 2.0 B Male to USB Type-C (USB-C) Male cable
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in
- 28AWG Data Pair / 22AWG Power Pair; Supports 1.5A current

System Requirements

- A device with a USB Type-B connector
- A tablet, laptop, ultrabook or computer with an available USB Type-C (USB-C) port

Package Includes

- USB 2.0 B Male to USB Type-C (USB-C) Male Cable - 6-ft

Specifications

OVERVIEW	
UPC Code	037332188588
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight

Downloaded from Arrow.com.

PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5MM
Wire Gauge (AWG)	28/22
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Relative Humidity	10% to 85%, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.