


DATE	REV	ECN	APP'D. BY
05/17/17	A0	Released	HU
08/07/17	A1	11059	KC
12/03/19	A2	11479	ADB
7/12/22	A3	12018	JMM
09/18/23	A4	12250	GWL



Notes:

- 1) Each cable assembly to be individually bagged.
- 2) 50μ" Gold plating on contacts
- 3) Cable Construction:
 - 24AWG Stranded
 - 4Pr, F/UTP, Type CM
 - PVC Jacket
- 4) Assembled Strain Relief
Color to match Jacket color

P/N Key:

BC-5Sxyyyz

UOM
M = Meters
F = Feet

Length
Meters = xx.x (00.3 - 30.0)
Feet = xxx (001 - 100)


Color
E = Blue O = Orange
G = Grey R = Red
K = Black W = White
N = Green Y = Yellow

O/A Length Tolerance:

<u>Metric</u>	
0 ~ 200mm	±10mm
201 ~ 1000mm	±20mm
1001 ~ 1500mm	±25mm
1501 ~ 2100mm	±30mm
>2100mm	±40mm

<u>Imperial</u>	
0 ~ 1ft	±0.5in
2ft ~ 3ft	±0.75in
4ft ~ 7ft	±1.0in
> 7ft	±1.5in

Wiring Map: 568B Standard



Example Parts Numbers

Meters		
P/N	Color	Length
BC-5SG010M	Grey	1.0m
BC-5SE050M	Blue	5.0m
BC-5SE100M	Blue	10.0m

For Part Numbers Not Shown Follow Part Number Key Format

CABLE MARKING:

350MHz (UL) E305668 TYPE CM 24AWG 75°C C(UL) E305668
 CM 75°C ETL VERIFIED ANSI/TIA-568.2-D STP CAT.5E
 SHIELDED RoHS COMPLIANCE MSL-VN- BATCH NO.

THIRD ANGLE PROJECTION			300 Executive Drive, Suite 300 West Orange, NJ, 07052 +1 201 432 0463 http://www.belfuse.com
DO NOT SCALE DRAWING	TITLE: Bel Patchcord Assembly, C5e F/UTP		
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	DRN BY: XYQ DATE 05/17/17		
DIMENSIONS: INCHES [METRIC]	APPD BY: HU DATE 05/17/17		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°	THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.		
SHEET NO. 1 OF 1	DWG NO. CT999140		REV. A4

