



Part Number : [194320015](#)

Product Description : MX150L 2 Circuit Female Sealed Receptacle for 12-10 AWG Wire, without CPA

Series Number : 19432

Status : Active

Product Category : Connector Housings




Documents and Resources

Drawings

[194320015_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Connector Housings
Series	19432
Description	MX150L 2 Circuit Female Sealed Receptacle for 12-10 AWG Wire, without CPA
Application	Power, Wire-to-Wire
Comments	Mat Seal Color is Yellow, Polarized to Mating Part; IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Product Name	MX150L
UPC	800756927909

Agency

CSA	LR18689
UL	E152602

Physical

Circuits Detail	1x1
Circuits (maximum)	2
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Net Weight	22.790/g

Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150L 2 Circuit Plug for 12-10 AWG Wire	<u>194330013</u>

Use with Part(s)

Description	Part Number
MX150L Female Terminals	<u>19434</u>

This document was generated on Apr 22, 2026