



Color: ■ gray

Mounting accessories *WINSTA®* MINI 2-pole

Put your trust in tried-and-tested accuracy for the electrical installation in your project: The mounting accessories from the *WINSTA®* MINI product line. With WAGO, you get enjoy the advantages of a large selection of expansions for the *WINSTA®* product line. Where space is tight, our smallest pluggable connection system, *WINSTA®* MINI, conveniently displays its advantageous properties. It saves space, and, with Push-in *CAGE CLAMP®* spring pressure connection technology, it additionally saves time, since the connection is low-maintenance and can be performed without screw connections.

Push-in *CAGE CLAMP®* spring pressure connection technology – pluggable installation instead of laborious screw connections!

The *WINSTA®* Pluggable Connection System is perfectly tailored to the strict requirements of building installation. It makes electrical installation plug-gable, and therefore faster, even more reliable, and error-free. Use of this pre-assembled system decreases time spent on assembly and errors during installation at the construction site. Choose quality and durability – with protection against mismatching from WAGO makes the installation of electrical components substantially easier.

- easy tool-free operation, a wide range of coding options
- fast, secure installation

Notes	
General safety information	NOTICE: Observe installation and safety instructions! 1. Only to be used by a qualified electrician or by a person electrically instructed for the task (EIP per DIN VDE 0105-100). 2. Do not install while energized or under load. 3. Use only for its intended purpose. 4. Observe applicable national regulations, standards and directives. 5. Observe the technical specifications of the products. 6. Ensure correct polarity assignment. 7. Do not use damaged or contaminated components. 8. Observe conductor types, conductor cross-sections, strip lengths and cable diameters. 9. Insert conductors up to the stop. 10. Use only with locking lever and strain relief. 11. Use original accessories only. To be sold only with installation instructions!



Connection Data

Connection 1	
Pole number	2

Physical data

Width	12.5 mm / 0.492 inches
Height	18.9 mm / 0.744 inches
Depth	10.5 mm / 0.413 inches

Mechanical data

Suitable	for socket and plug
----------	---------------------

Material data

Note (material data)	Information on material specifications can be found here
Color	gray
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.012 MJ
Weight	0.4 g

Environmental requirements

Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

Commercial data

Product Group	20 (Winsta)
PU (SPU)	100 (50) pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143838511
Customs tariff number	39269097900

Product Classification

UNSPSC	39121421
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 9.0	EC002863
ETIM 10.0	EC002863
ECCN	NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 890-302	↓

Documentation

Bid Text			
890-302	16.03.2015	doc 23.50 KB	↓
890-302	19.02.2019	xml 2.66 KB	↓

CAD/CAE-Data

CAD data	
2D/3D Models 890-302	↓