

BIT E6,3 0,6X3,5X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

General ordering data

Version	Accessories, Screwdriver insert
Order No.	9024020000
Type	BIT E6,3 0,6X3,5X70
GTIN (EAN)	4008190852627
Qty.	5 items
Delivery status	Discontinued
Available until	2021-01-31T00:00:00+01:00
Alternative product	BIT E6,3 0,6X3,5X70

BIT E6,3 0,6X3,5X70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

ROHS	Conform
------	---------

Dimensions and weights

Width	70 mm	Width (inches)	2.7559 inch
Net weight	9.4 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Bit with slotted blade, 0.6 x 3.5 x 70
------------------------	---

Electric screwdriver

Weight	9.6 g
--------	-------

Screwing tools

Blade width (B)	3.5 mm	Blade thickness (A)	0.6 mm
Form	E 6.3 DIN 3126, Slotted	Blade length	70 mm

Classifications

ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 14.0	21-04-42-04
ECLASS 15.0	21-04-42-04		