



+ CONNECTORS

AUTOMOTIVE CONNECTOR CAPS & COVERS



✓ Active

TE CONNECTIVITY (TE)
SOC CONN CVR ASSY,4POS,AMPSEAL 16,90 DEG
[AMP](#) | [AMPSEAL 16](#)

2302492-3
TE Internal Number: 2302492-3

- [EU RoHS Compliant](#)
- [EU ELV Compliant](#)
- Connector System** Wire-to-Wire
- Accessory Type** Backshell Kit
- Cable Exit Angle** 90
- Sealable** No
- Strain Relief** With

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings
BACKSHELL AND ELBOW KIT, 4 POSN PLUG ASSY, AMPSEAL 16
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

108-151043

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

INSTRUCTION SHEET, AMPSEAL 16 BACKSHELLS, VERTICAL AND RIGHT ANGLE

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Wire

Accessory Type Backshell Kit

Sealable No

Strain Relief With

Configuration Features

Number of Positions 4

Body Features

Cable Exit Angle 90

Color Black

Material PA

Usage Conditions

Operating Temperature Range -40 – 125 °C [-40 – 257 °F]

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Method Bag/Box

Other

Serviceable Yes

Statement of Compliance

Statement of Compliance

PDF