


CnC Tech

CABLE SPECIFICATION

Style	4703-12-1-0500-001-1-TS		
Spec.	UL 12AWG /		
	29UL11064BK001	Version	A0
Item		Unit	Specification
Awg		AWG	12
No. of conductor		p,c	1C
Conductor	Material	---	Tinned Copper
	Construction	No./mm	65/0.254±0.008
	Stranded diameter	mm	2.36(Ref.)
Insulation	Material	---	XLPE
	Nom. Thickness	mm	1.2(Ref.)
	Diameter	mm	4.8±0.15
	Color	---	White
Jacket	Material	---	XLPE
	Min. Thickness	mm	0.76
	Nom. Thickness	mm	0.8(Ref.)
	O.D	mm	6.4±0.15
	Color	---	Black
Marking	(UL) E484134 PV WIRE 12AWG 90°C WET OR DRY 1000 OR 2000V SUN RES -40°C		
	White		

Configuration:

- 1.Working temp -40°C~+90°C.
- 2.Compliant with UL4703.
- 3.500FT/Reel.



Sectional view

RATIFY	<i>Xuqiu</i>	APPROVED	/	DESIGN	<i>Zhuoqing</i>
--------	--------------	----------	---	--------	-----------------

HJ-RNE-001-A0