© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

RF CONNECTORS



✔ Active

TE CONNECTIVITY (TE)

BNC Pnl Skt 75Ohm Silver Pltd

Miniature Coax | SKF , SKT

1-1337446-1
TE Internal Number: 1-1337446-1

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Connector Interface BNC

Connector Style Jack

Mated Outer Diameter (Approximate) 14.529 mm [.572 in]

Impedance (Ω) 75

Operating Frequency (GHz) 2

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

BNC PANEL SOCKET 50 OHM & 75 OHM
PDF
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Downloaded from Arrow.com.

Connector Interface BNC
Connector Style Jack
Sealable No

Configuration Features

Number of Positions 1

Electrical Characteristics

Impedance (Ω) 75

Body Features

Body Material Brass
Body Plating Material Silver
Body Insulation With

Contact Features

Center Contact Plating Material Silver
Center Contact Material Brass

Termination Features

Termination Method to Wire & Cable Solder Terminal

Mechanical Attachment

Panel Mount Retention Type Flange
Connector Mounting Type Panel
Panel Attachment Style Front Mount, Rear Mount

Dimensions

Mated Outer Diameter (Approximate) 14.529 mm [.572 in]
Panel Cutout 1 x 12.0 + 4 x 3.2 Rear Mount, 1 x 9.0 + 4 x 3.2 Front Mount

Operation/Application

Operating Frequency (GHz) 2

Packaging Features

Packaging Method Box
Packaging Quantity 50

Other

Dielectric Material PTFE
Grade Professional

PRODUCT COMPLIANCE

Statement of Compliance

Downloaded from Arrow.com.

Statement of Compliance

PDF

Downloaded from Arrow.com.