






ROHS PART NUMBER

PART NUMBER	
200 Mating	D50P91C4GV00LF
500 Mating	D50P91C6GV00LF



PC board drilling dimensions
(after plating – thickness: 1.60 to 3.20 mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface			tolerance			projection		product family		
				ISO 1302			ISO 406			ISO 1101		D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified			tolerances unless otherwise specified			mm		title		
E	LS06-0074	MPE	2006-05-09	angles			linear			scale 2:1		MALE CONNECTOR DELTA D 50		
F	LS06-0097	LGO	2006-07-29	0°±2°								STRAIGHT PRESS FIT		
G	LS06-0140	LGO	2006-09-22											
H	111-0062	MINI	2011-04-04	dr			PESSON					dwg no		
J	ELX-I-24020	AAB	2016-06-06	engr			MITHUN PAUL					sheet 1 of 1		
				chr			ATHUL A.B					C01-8646-0256		
				appd			BIJU K PAUL					A3		
												type		
												Product Customer Drawing		
sheet index	revision	J												
	sheet	1												