

USB-C Multiport Adapter, DVI, USB-A Port, Gbe and PD Charging, Black

MODEL NUMBER: **U444-06N-DGUB-C**



Adds DVI, USB-A, USB-C PD charging and Gigabit Ethernet ports to your tablet, laptop, notebook, smartphone or PC.

Features

Mini Docking Station Turns Your Device's USB-C or Thunderbolt 3 Port into a Multiport Workstation This USB Type-C to DVI adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting video to a large display, adding a thumb drive or other USB peripheral, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

Supports USB DisplayPort Alternate Mode for Transmitting DisplayPort and USB Signals With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 1080p Video to a DVI Display To send high-definition video to a DVI television, projector or monitor, connect the DVI port to the display using a DVI cable (sold separately). The DVI port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz.

Connects a USB Peripheral The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer. It supports fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and is backward compatible with USB 2.0 and USB 1.1 devices. This dedicated port provides up to 1.5A of fast-charging power to mobile devices.

Charges a Connected Device The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the U444-06N-DGUB-C is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W).

Accesses a Wired Gigabit Ethernet Network The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play Thunderbolt 3 to DVI adapter requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design The U444-06N-DGUB-C comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Transmits DisplayPort signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Connects you to a wired Ethernet network when no Wi-Fi is available
- BC 1.2-compliant USB-A port provides up to 1.5A of fast-charging power
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks
- Easy installation with plug-and-play operation—no software required

Applications

- Play 1080p video from your laptop or PC on a DVI display
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Transfer data from a USB flash drive or connect your computer to a USB printer or other USB device
- Charge your connected notebook or laptop by connecting its wall charger to the USB-C PD Charging port

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB DisplayPort Alternate
Mode

- Display device with DVI input
(DVI port)

Package Includes

- U444-06N-DGUB-C USB-C to
DVI Adapter with USB-A Hub,
Gigabit Ethernet, Thunderbolt 3,
1080p—PD Charging, Black
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332209122
Product Type	Multiport Adapter
Host Connector	USB C (MALE)
VIDEO	
Extended Mode	No
Mirror Mode	No
Number of Monitors Supported	1
Resolutions Supported	DVI: 1080P 60Hz (1920 x 1200)
Video Ports	DVI-I DUAL LINK (FEMALE)
Video Ports Detail	HDCP 1.3
DATA	
Data Ports	USB A (FEMALE)
Data Ports Detail	USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Bus Powered	Yes
Product Length (in.)	6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
CHARGING	
Charging Ports / Amps	1.5A; 3A
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0); USB-A: 5V 1.5A (7.5W)
USB Power Delivery (PD) Charging Support	Yes
Total Charging Watts	60
USB Power Delivery (PD) Charging Specification	2.0
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	PVC, ABS
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.50
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / in.)	0.65 x 3.8 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.09
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	8.3 BTU/Hr
Power Consumption (Watts)	2.4
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB-A), Up to 20V 3A (60W) Input (USB-C)
COMMUNICATIONS	
Network Speed	Gigabit Ethernet (10/100/1000)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

IEEE Standards Supported	802.3; 802.3u; 802.3az; 802.3x
CONNECTIONS	
Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 2	USB 3.0 A (FEMALE)
Side B - Connector 3	RJ45 (FEMALE)
Side B - Connector 4	USB Type-C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	DVI: 1920 X 1080 (1080P) @ 60HZ
HDCP Specification	1.3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Technology	Cat5/5e; Cat6; USB 3.1 (Gen 1); DVI; USB; PD Charging
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>