




PRODUCT NUMBER

PITCH

HWxxB0x000J0G

2.50 mm



2P

Material:

- Item①Insulator(lever):Thermoplastic (UL94V-0) Orange(RAL2011/P)
- Item②Bottom body:Thermoplastic (UL94V-0)
- Item③Spring clamp:Stainless steel
- Item④Female contact: PhBz.Tin plated
- Item⑤Top body:Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 150V
- Current rating: 4A
- Wire range:
- Solid wire(AWG): 20-28
- Stranded wire(AWG): 20-28
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus

PART NO.: HW xx B 0 x 0 00J0 G

N=NUMBER OF POLES

Dim A=N×2.50+0.60	
Dim B=(N-1)×2.50	
Dim C=N×2.50	
Poles	Tolerance
2P-6P	±0.10
7P-12P	±0.15
13P-18P	±0.20
19P-24P	±0.30

Solid block		Color		RoHS compliant (lead<4%) In copper Alloy
No. of poles				
02 2 poles		0 Black (RAL9005)		
03 3 poles		2 Red (RAL3001/D)		
...		3 Orange(RAL2011/P)		
24 24 poles		4 Yellow(RAL1018/A)		
		5 Green(RAL6018/T)		
		6 Blue (RAL5015/A)		
		8 Grey(RAL7035/D)		
		9 White(RAL1102)		
		C Green(RAL6018/U)		

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family	
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	TERMINAL BLOCK	
					angles		title	
					0.1		TERMINAL BLOCK	
					0.2		SPRING CLAMP, PLUGGABLE PLUG	
					X*±1"		scale	
					dr	EVIN ZHONG 051514	dwg no	
					enrg	EVIN ZHONG 051514	sheet 1 of 1 size	
					chr	HANKE FENG 051514	HWxxB0x000J0G	
					appd	SHI JUN 051514	type	
							CUSTOMER Drawing	
sheet index	revision	A						