

## 3.5 mm Mini Stereo to RCA Audio Y Splitter Adapter Cable (M/2xM), 12 ft. (3.7 m)

MODEL NUMBER: P314-012



### Highlights

- Audio Cable Y Adapter 3.5 mm-M/(2)RCA-M - 12 ft.
- Connect a device with a 3.5 mm jack to a sound system with RCA inputs or a sound system with RCA inputs to a device with a 3.5 mm jack
- Perfect for your PC, notebook, MP3 player or iPod
- Molded cable with built-in strain relief

### Package Includes

Audio Y Splitter Adapter 3.5MM Plug/2 RCA Plugs, 12 ft. (3.7 m)

### Description

12-foot (3.7 m) audio Y splitter/adapter cable. This cable has a 3.5 mm plug on one end and two RCA plugs on the other. Enables a PC sound card, portable CD player, MP3 player, iPod or any other audio device with a 3.5 mm mini-stereo jack to connect to an audio device with RCA audio inputs or an audio device with RCA audio inputs to connect to a PC sound card, portable CD player, MP3 player, iPod or any other audio device with 3.5 mm mini-stereo jack.

### Features

- Molded cables with built-in strain relief
- 3.5mm (male) to (2x) RCA (male)

## Specifications

| OVERVIEW                       |                |
|--------------------------------|----------------|
| UPC Code                       | 037332012159   |
| Product Type                   | Passive Cable  |
| Technology                     | Stereo Audio   |
| Cable Type                     | Passive        |
| CONNECTIONS                    |                |
| Side A - Connector 1           | 3.5MM (MALE)   |
| Side B - Connector 1           | (2) RCA (MALE) |
| Latching or Gripping Connector | No             |
| PHYSICAL                       |                |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                           |
|--------------------------------------|---------------------------|
| Color                                | Black                     |
| Cable Jacket Color                   | Black                     |
| Cable Length (ft.)                   | 12                        |
| Cable Length (m)                     | 3.66                      |
| Cable Length (in.)                   | 72                        |
| Shipping Dimensions (hwd / in.)      | 7.00 x 9.00 x 0.50        |
| Shipping Dimensions (hwd / cm)       | 17.78 x 22.86 x 1.27      |
| Shipping Weight (lbs.)               | 0.16                      |
| Shipping Weight (kg)                 | 0.07                      |
| Unit Dimensions (hwd / in.)          | 0.000 x 0.000 x 0.000     |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                           |
| IP68 Rated                           | No                        |
| IP20 Rated                           | No                        |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                           |
| Product Compliance                   | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>        |                           |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.