Part Number : 2065230163
Product Description : Mini50 Unsealed Receptacle, Dual Row, UL 94 HB, without CPA, 16 Circuits, Polarization Option C, Dark Gray
Series Number : 206523
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2065230163_sd.pdf

PK-31301-538-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2065230000-AS-000.pdf

2065230000-AS-CH-000.pdf

2065230000-AS-KR-000.pdf

2065230000-PS-000.pdf

2065230000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	206523
Description	Mini50 Unsealed Receptacle, Dual Row, UL 94 HB, without CPA, 16 Circuits, Polarization Option C, Dark Gray
Application	Automotive, Power, Wire-to-Board
Product Name	Mini50
UPC	191130110032

Physical

Circuits (maximum)	16
Color - Resin	Gray (Dark)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes

Downloaded from Arrow.com.

Material - Resin	PBT
Net Weight	1.687/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarization	C
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Header, UL 94 HB, Right-Angle, SMT, Dual Row, 16 Circuits, Tin (Sn) Plating, Polarization Option C, Dark Gray, Tape and Reel	348978162
Mini50 Unsealed Header, UL 94 HB, Right-Angle, SMT, Dual Row, 16 Circuits, Tin (Sn) Plating, Polarization Option C, Dark Gray, Tube	348979162
Mini50 Unsealed Vertical Header, UL 94 HB, Dual Row, 16 Circuit, Polarization Option C, Dark Gray, Tray	348250162
Mini50 Unsealed Vertical Header, UL 94 HB, Dual Row, 16 Circuit, Polarization Option C, Dark Gray, Tube	348259162
Mini50 Unsealed Right-Angle Header, UL 94 HB, Dual Row, 16 Circuit, Polarization Option C, 2.80mm Pin Length, Dark Gray, Tray	348260162

Downloaded from Arrow.com.

Mini50 Unsealed Right-Angle Header, UL 94 HB, Dual Row, 16 Circuit, Polarization Option C, 2.80mm Pin Length, Dark Gray, Tube	348269162

Use with Part(s)

Description	Part Number
CTX50 Unsealed Receptacle Terminals	560023

Downloaded from Arrow.com.