Product Details for 603324 -5

No Image Available

603324 -5

Active

Heat Shrink Tubing

RoHS Compliant (Statement of Compliance)

Product Highlights:

- Jacket Tubing
- General Purpose Application
- Operating Temperature = -30 - 125 °C
- Inside Diameter (Min -Max) = 1.57 - 3.18 mm
- Without Sealant

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- AMPSULATION VFP21 AND FP21, (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- Heat Shrink Tubing (PDF, English)

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Jacket Tubing
- Sealant = Without
- Style = VFP21
- Size = 3.18 [.125]
- Color = Black
- Material = Polyolefin
- Proprietary Name = AMPSULATION

Body Related Features:
- Marked = Yes
- Shrink Ratio = 2:1
- Wall Style = Thin
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 0.51 [0.020]
- Length (M [ft]) = 152.40 [500.00]
- Marking Color = White

Housing Related Features:
- Inside Diameter (Min -Max) (mm [in]) = 1.57 – 3.18 [0.062 – 0.125]

Industry Standards:
- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:
- Operating Temperature (°C) = -30 – +125

Operation/Application:
- Application = General Purpose

Packaging Related Features:
- Packaging Method = Reel
- Weight per Linear Foot (g [lb]) = 1.089 [0.0024]

Other:
- Brand = AMP

© 2006 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.