



**Part Number :** [1300940385](#)  
**Product Description :** Standard Duty Support Grip,  
Single "U" Eye, Split Rod, Single Weave, Cable Diameter  
12.70-15.49mm (.500-.610"), Approximate Break  
Strength 349.27kg (770 lbs)  
**Series Number :** 130094  
**Status :** Active  
**Product Category :** Cable Grips  
**Engineering Number :** 35285



## Documents & Resources

### Drawings

[PK-130227-004-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Single "U" Eye, Split Rod, Single Weave, Cable Diameter 12.70-15.49mm (.500-.610"), Approximate Break Strength 349.27kg (770 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835285

### Agency

CSA	LR32159
-----	---------

### Physical

Approximate Break Strength	349.27kg (770 lbs)
Bale Length	0.178m (7.00")
Body Style	Straight
Cable Diameter	12.70-15.49mm (.500-.610")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.279m (11.00")
Net Weight	1.000/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

---

This document was generated on Sep 22, 2025