

PRODUCTS

Rocker switches

Pushbutton switches

Toggle switches

Slide switches

Rotary switches

Foot switches

Tact and key switches

Snap-action switches

Micro-signal switches

ECO switches

Sensors

Systems and modules

Accessories

General information

Catalog request /
download

PRODUCTS ▶ SNAP-ACTION SWITCHES

Snap-action switches

SERIES 1055 - SUBSUBMINIATURE SNAP-ACTION SWITCHES IP 67 - TO 4 A 12 V
OR 2 A 24 V DC

◀ Show previous product

Show next product ▶

1056.3060

Drawing

Similar to original
product

→ Print data sheet

Product number	1056.3060
Miscellaneous	without pin
Switching function	Changeover switch (SPDT momentary)
Number of poles	1-pole
connections	PCB terminal, coded, cranked
Mechanical life endurance	5E5
Rating IEC	2 A 24 V DC (ohmsche Last) 4 A 12 V DC (ohmsche Last)
Contact resistance (new condition)	< 50 mOhm
Insulation resistance (new condition)	> 100 (500 V DC) MOhm
Protection type	Connection IP 00
Ambient temperature	-40 °C ... +85 °C
Flammability	UL 94 HB
Actuators and additional actuators	POM, standard actuator
Housing description	PBTP
Contact material	Au
Operating force	≥ 1.3 N
Difference travel max.	0.4 mm
Free position (FP) max.	11.5 mm
Operating position (OP)	10.5 ±0.3 mm
Permissible total travel position	9 mm