Pushing Performance
Since 1945

Han 16B Docking Frame IP67 fixed



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 016 1710
Specification	Han 16B Docking Frame IP67 fixed
HARTING eCatalogue	https://harting.com/09300161710

Identification

Category	Accessories
Type of accessory	Docking frame

Version

Size	16 B
Details	Pull-in-range x-axis: ± 1 mm Pull-in-range y-axis: ± 1 mm Pull-in-range z-axis: - 0.5 / +1 mm

Technical characteristics

Mating cycles	≥10,000
Note on the mating cycles	Mating cycles with other HMC components
Degree of protection acc. to IEC 60529	IP65 / IP67

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (accessories)	Stainless steel

Commercial data

Packaging size	1
Net weight	255.8 g

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Commercial data

Country of origin	China
European customs tariff number	85389099
GTIN	5713140572317
eCl@ss	27440206 Module carrier frame for industrial connectors
ETIM	EC002312
UNSPSC 24.0	39121421

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.