


| LOC | DIST | REVISIONS |     |             |           |     |      |
|-----|------|-----------|-----|-------------|-----------|-----|------|
|     |      | P         | LTR | DESCRIPTION | DATE      | DWN | APVD |
| CE  | 16   |           | A3  | ADDED 9-9   | 18SEP2013 | HZ  | RZ   |

- 1

MAXIMUM CONNECTOR INSERTION LOSS IS 0.40dB PLUS CABLE ATTENUATION OF 0.70dB/km AT 1300nm. (SEE TABLE)
2. MINIMUM RETURN LOSS: 55dB
3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



|                          |                               |             |
|--------------------------|-------------------------------|-------------|
| 1.10                     | 1000.00±20.00 [39370.1±787.4] | 9-5492015-9 |
| 0.44                     | 50.00±0.50 [1968.5±19.7]      | 5-5492015-0 |
| 0.41                     | 12.19±0.15 [480.0±5.9]        | 3-5492015-2 |
| 0.40                     | 1.37±0.05 [53.9±2.0]          | 3-5492015-1 |
| 0.40                     | 0.46±0.03 [18.1±1.0]          | 3-5492015-0 |
| 0.47                     | 100.00±1.00 [3937.0±39.4]     | 2-5492015-9 |
| 0.44                     | 60.00±0.60 [2362.2±23.6]      | 2-5492015-5 |
| 0.43                     | 40.00±0.40 [1574.8±15.8]      | 2-5492015-2 |
| 0.42                     | 30.00±0.30 [1181.1±11.8]      | 2-5492015-1 |
| 0.42                     | 35.00±0.35 [1378.0±13.8]      | 2-5492015-0 |
| 0.40                     | 4.00±0.08 [157.5±3.2]         | 1-5492015-9 |
| 0.41                     | 25.00±0.30 [984.0±11.8]       | 1-5492015-6 |
| 0.41                     | 9.00±0.15 [354.3±5.9]         | 1-5492015-4 |
| 0.41                     | 8.00±0.15 [315.0±5.9]         | 1-5492015-3 |
| 0.40                     | 6.00±0.08 [236.2±3.0]         | 1-5492015-2 |
| 0.40                     | 1.50±0.05 [59.1±2.0]          | 1-5492015-1 |
| 0.40                     | 0.75±0.03 [29.6±1.0]          | 1-5492015-0 |
| 0.40                     | 0.30+0.05/-0.0 [11.8+2.0/-0]  | 5492015-9   |
| 0.40                     | 7.00±0.08 [275.6±3.2]         | 5492015-8   |
| 0.41                     | 20.00±0.30 [787.4±11.8]       | 5492015-7   |
| 0.41                     | 15.00±0.15 [591.6±5.9]        | 5492015-6   |
| 0.41                     | 10.00±0.15 [393.7±5.9]        | 5492015-5   |
| 0.40                     | 5.00±0.08 [196.8±3.2]         | 5492015-4   |
| 0.40                     | 3.00±0.05 [118.1±2.0]         | 5492015-3   |
| 0.40                     | 2.00±0.05 [78.7±2.0]          | 5492015-2   |
| 0.40                     | 1.00±0.05 [39.4±2.0]          | 5492015-1   |
| <div>1</div> MAX IL (dB) | L METERS [INCHES]             | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN  
J. W. DAVIS  
21OCT05

CHK  
J. DUNCAN  
21OCT05

APVD  
F. McCORKEL  
21OCT05

DIMENSIONS:  
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± -  
4 PLC ± -  
ANGLES ± -  
FINISH -

MATERIAL  
-

FINISH  
-

PRODUCT SPEC  
-

APPLICATION SPEC  
-

WEIGHT  
-

21OCT05

21OCT05

21OCT05

TE Connectivity

CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE 2.9mm OFNR CABLE, SC TO SC, RoHS

SIZE  
A2

CAGE CODE  
00779

DRAWING NO  
C-5492015

RESTRICTED TO  
-

CUSTOMER DRAWING

SCALE  
NTS

SHEET  
1 OF 1

REV  
A3