



NOTES:
1. INSERTION LOSS: 1.0 dB MAX.
2. MATERIALS:
   HOUSING - DELRIN, BLACK
   TOSLINK ADAPTER - ABS
   CENTER PIN - BRASS, GOLD PLATED
   DUST CAPS - PVC
3. FOR SCREWS TO BE SHIPPED WITH ASSEMBLY AND INDIVIDUAL PACKAGING, ADD SUFFIX -PKG TO PART NUMBER.
4. WHEN MOUNTING ASSEMBLY, USE A SCREW TORQUE OF 10 INCH-POUNDS MAXIMUM.
5. THIS PRODUCT IS RoHS COMPLIANT.



RECOMMENDED
PANEL CUT-OUT

CUSTOMER DRAWING

REV	ECO NUMBER	DATE	BY	APVD
B	26950	5-7-12	TO	TJK
A	26347	2/26/09	RS	TJK

REVISIONS

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES
   - TWO PLACE DECIMALS ±0.02
   - THREE PLACE DECIMALS ±0.005

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE	WIDTH	MULT	LBS/M	TEMPER

FINISH
SPEC No.

MATERIAL SEE NOTES
SPEC No.

FIRST USED ON

SCALE 3:2

DATE DRAWN	BY	CHKD	APVD
5/12/08	JGK	RS 6/8/09	TJK 7/20/09

Switchcraft®

SHEET 1 OF 1

NAME E SERIES TOSLINK ADAPTER, RoHS

PART No. EHTL2

REV B

SolidWorks CAD File

A

Downloaded from Arrow.com.