







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/27/20	
A		UPDATE PACKING	7/2/20	OW/NL
B		UPDATE DRAWING	3/18/21	WX/NL
C		UPDATE PACKING	5/28/21	WX/NL



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 125 AC max

Current rating: 2 Amp max

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Halogen & Lead free, RoHS compliant



PACKAGED ON PLASTIC TUBE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			<div>ADAM TECH</div>		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS					TITLE	
DRAWN		LH	5/27/20		.079 [2.00] SHROUDED HEADER STRAIGHT, PCB, TIN PLATED	
CHECKED		NL	5/27/20			
APPROVED						
REF: S00111C			SCALE: NTS		SHEET 1 OF 2	

6

5

4

3

2



1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-----	-------	-------------	------	------

SEE SHT 1 OF 2 FOR REVISION



1 TUBE/66 PCS

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS DATE

DRAWN LH 5/27/20

CHECKED NL 5/27/20

APPROVED

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.079 [2.00] SHROUDED HEADER
STRAIGHT, PCB, TIN PLATED

SIZE	PART NO.	REV.
X	2SH-J-03-TS-PT	C

REF: S00111C SCALE: NTS SHEET 2 OF 2

6

5

4

3

2

1