



Search within category

GO

BUY NOW

DESIGN / INSTALL

PUME925-4E-C350



Heavy Duty Fir Tree Push Mount with 15" Wide Strap Cable Tie Assembly, hole size 0.354", Heat Stabilized, Impact Modified, Weather Resistant Nylon 6.6.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

| | |
|---------------------------------|---------------------------|
| Compatible Cable Tie | M, I, S, LH, H, EH |
| Mount Method | Fir Tree Hole Mount |
| Material | Heat Stabilized Nylon 6.6 |
| Overall Height (In.) | 1.1 |
| Overall Height (mm) | 28 |
| Color | Black |
| Head Diameter (In.) | 1.80 |
| Head Diameter (mm) | 30.0 |
| Maximum Bundle Diameter (In.) | 4.13 |
| Maximum Bundle Diameter (mm) | 105.0 |
| Panel Hole Diameter Range (In.) | 0.34 - 0.36 |
| Panel Hole Diameter Range (mm) | 8.8 - 9.3 |
| Panel Thickness Range (In.) | 0.04 - 0.62 |
| Panel Thickness Range (mm) | 1.0 - 16.0 |
| Panel to Top of Mount (In.) | 0.27 |
| Panel to Top of Mount (mm) | 7.0 |
| Surface Treatment | Other |
| Type | Through Hole |
| Type of fastening | Plug-in mounting |
| RoHS Compliancy Status | Compliant |
| Min. Order Qty. | 100 |