

15

1503 30


Jack connectors



Jack chassis socket acc. to JIS C 6560 JC35J3A, 3.5 mm, 3 poles/stereo, angular version, for printed circuit boards

15

1503 30



Environmental conditions

Temperature range -20 °C/+70 °C

Materials

Insulating body PBT, V0 according to UL94
Contact spring CuSn/CuZn, silver-plated

Mechanical data

Mating cycles 5000
Insertion force 3–30 N¹
Withdrawal force 3–30 N¹

¹ measured with a gauge plug

Electrical data (at T_{amb} 20 °C)

Contact resistance ≤ 30 mΩ
Rated current 1 A
Rated voltage 34 V
Rated impulse voltage 500 V/60 s
Insulation resistance ≥ 100 MΩ

Associated products

Counterparts
 ☞ 1532 07 ☞ 1532 10 ☞ 1532 11
 ☞ KLS 40 ☞ KLS 44 ☞ WKLS 40

*a printed circuit board layout, components side view

15

1503 30

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
1503 30	3	500	1000

Packaging:

in bulk, in a cardboard box or a plastic bag