Specifications



Photo is representative





Eaton HCMA1104-R36-R

Eaton HCMA1104 inductor, 0.36 uH, 30 A Irms, 42 A ISAT, 1.19 mΩ resistance, SMT mounting, Iron Powder, 2-pins, 850 qty.

General specifications	
PRODUCT NAME	Eaton HCMA1104 inductor
CATALOG NUMBER	HCMA1104-R36-R
UPC	051712514330
PRODUCT LENGTH/DEPTH	11.5 mm
PRODUCT HEIGHT	4 mm
PRODUCT WIDTH	10.3 mm
PRODUCT WEIGHT	2.49 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	30 A
ISAT	42 A
PACKAGE QUANTITY	850
MATERIAL	Iron powder
AUTOMOTIVE GRADE	Yes
FREQUENCY RATING	Up to 5 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-55 to 125 °C
RESISTANCE	1.19 mΩ
SIZE	11.5x10.3x4.0 mm
TERMINALS	2 Pads
SERIES	HCMA1104

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - HCMA1104-R36-R Eaton HCMA1104 automotive high current power inductors data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.