

Part Number : [39000278](#)

Product Description : 1.57mm Diameter,
Standard .062" Pin and Socket Crimp Terminal, Series
1560, Male, with Tin (Sn) Plated Brass Contact, 24-18
AWG, Reel

Series Number : 1560

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 1560T



Documents and Resources

Drawings

[039000278_sd.pdf](#)

[15600000-PK-000.pdf](#)

[SPK-1560-001-001.pdf](#)

[SPK-1560-001-002.pdf](#)

[SPK-1560-001-003.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-1625-010-001.pdf](#)

[15600000-TS-000.pdf](#)


Tooling Specifications

[CS-1560_1561-001.pdf](#)

[CS-1560_1561-002.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant

Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	1560
Description	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 24-18 AWG, Reel
Application	Power, Wire-to-Wire
Product Name	Standard .062"
UPC	800753330252

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	123.700/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.50-3.10mm
Wire Size (AWG)	18, 20, 22, 24
Wire Size mm ²	N/A

Application Tooling

Global

Description	Part Number
Insertion Tool for Standard .062" Diameter Male and Female Terminals	<u>11020001</u>
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	<u>11030002</u>
Hand Crimp Tool for Standard 1.57mm Pin and Socket Crimp Terminals, 24-18 AWG	<u>638191300</u>
Mini-Mac Applicator for Standard .062" Pin and Socket Terminals, for 24-18 AWG Wire with Insulation Diameter 1.52-3.05mm	<u>638914000</u>

Japan

Description	Part Number
Hand Extraction Tool	<u>11267034</u>

This document was generated on Jun 10, 2026