

Search within category

GO

BUY NOW

DESIGN / INSTALL



STP28X2MBU

Category 6A Performance, 28AWG, F/UTP Patch Cord, CM/LSZH, Blue, 2m.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Performance Level	Category 6A
Cable Color	Blue
Length (ft.)	6.56
Length (m)	2.0
Flammability Rating	CM, LSZH-1 (60332-1)
Termination End 1	Modular Plug
Termination End 2	Modular Plug
Standards	IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.
CE Compliant	Yes
Nominal Cable O.D. (In.)	0.19
Nominal Cable O.D. (mm)	4.7
Storage Temperature	-40°F to 158°F (-40°C to 70°C)
UL5A Listed	No
AWG Size	28
BMEcat - Type of Connector	RJ45 8(8)
Cable Type	F/UTP
Conductor Material	Copper
Installation Temperature	-40°F to 158°F (-40°C to 70°C)
Operating Temperature	14°F to 167°F (-10°C to 75°C)
RoHS Compliancy Status	Compliant
Min. Order Qty.	1