

PCF51JF128VLH :Part Detail

Product Summary Page

General Information

Package Information

Environmental and Compliance Information

Manufacturing Information

Ordering Information

Operating Characteristics

Reliability Data Lookup

General Information

Part Number	PCF51JF128VLH
Description	CMOS090SGTFS
Material Type	Tested Packaged Device
Life Cycle Description (code)	REMOVED FROM ACTIVE PORTFOLIO
Status	No Longer Manufactured

Package Information

Package Type and Termination Count	QFP 64
Package Description and Mechanical Drawing	LQFP 64 10*10*1.4P0.5
Device Weight(g)	0.34655
Package Material	Plastic
Mounting Style	Surface Mount
Package Length (nominal)(mm)	10.000
Package Width (nominal)(mm)	10.000
Package Thickness (nominal)(mm)	1.400
Maximum Height Above Board(mm)	1.600
Tape & Reel	No

Environmental and Compliance Information

Pb-Free	
RoHS Compliant	
Halogen Free	Yes
Material Composition Declaration (MCD)	Download MCD Report Download MCD Report
RoHS Certificate of Analysis (CoA)	Contact Us
2nd Level Interconnect	e3
Moisture Sensitivity Level (MSL)	3
Electrical Life	168 HOURS

Reliability Data Lookup

ABOUT NXP

[Investors](#)

[Partners](#)

[Careers](#)

RESOURCES

[Mobile Apps](#)

[Press, News, Blogs](#)

[Contact Us](#)

FOLLOW US



News 26 Apr 2017



NXP Delivers eDL and Vehicle
Registration Smartcards to Algeria

[Read More](#)

[Privacy](#) | [Terms of Use](#) | [Terms of Sale](#) | [Feedback](#)

©2006-2017 NXP Semiconductors. All rights reserved.