CUSTOMER PRINT


PART NUMBER: CA6C806SPXXX90


NOTES:

1. FINISHED PRODUCT TO BE COILED
2. OVERMOLD BOOT MATERIAL: UV PBT, BLACK
3. ELECTRICAL TEST: 100% CONTINUITY
4. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE


ASS'Y P/N	"X" DIM
CA6C806SP03990	3 FT. 3 1/2 IN. ±2 IN. [1M ±50.8mm]
CA6C806SP07990	6 FT. 7 IN. ±2 IN. [2M ±50.8mm]
CA6C806SP19790	16 FT. 5 IN. ±4 IN. [5M ±101.6mm]
CA6C806SP39490	32 FT. 9 3/4 IN. ±8 IN. [10M ±203.2mm]
CA6C806SPXXX90	

CABLE LENGTH IN "INCHES"





END "A"
FACE VIEW



WIRE COLOR CODE					
POS. 1	POS. 2	POS. 3	POS. 4	POS. 5	POS. 6
BLK	WHT	RED	BLU	GRN	YEL
16 AWG	16 AWG	20 AWG	20 AWG	20 AWG	20 AWG

DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS UNLESS INDICATED

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

RoHS COMPLIANT

REV.	INIT.	DATE	DESCRIPTION
A	MA	08-17-21	DRAWING CREATED PER DOR 21-109361DS-1

ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.

ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.

▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX

ORIG. DRAWN BY: MA DATE: 08-17-21

CHECKED BY:

APPROVED BY:

SCALE: NTS | SIZE: B | SHEET: 1 OF 1

FILE: CA6C806SPXXX90 | DIRECTORY: SLW

conxall

601 E. WILDWOOD VILLA PARK, IL 60181

TITLE: CABLE ASSEMBLY
2#16/4#20 SKT CONTACTS
INSTA-CLICK™ MINI-CON-X MIX SIG BULLET

CUSTOMER: STANDARD PRODUCT

PART NUMBER: CA6C806SPXXX90 | REV: A

Downloaded from Arrow.com.