
Part Number : 734123150
Product Description : MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, DU 40,000 Pieces, 50 Ohms
Series Number : 73269
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

734123150_sd.pdf

Specifications

735980780-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73269
Description	MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, DU 40,000 Pieces, 50 Ohms
Application	RF
Product Name	MCRF
Style	PCB
Type	Ultra-microminiature
UPC	198282942016

Electrical

Frequency	6 GHz
Impedance	50Ω

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	0.026/g
Orientation	Straight
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount
PCB Thickness - Recommended	N/A
Reverse Polar	No

Downloaded from Arrow.com.

Wire/Cable Type	N/A

This document was generated on Jan 28, 2026

Downloaded from Arrow.com.