



LOC	DIST	REVISIONS					
A1	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	new drawing	11FEB2002	—	—

Kontakt Contact	DGB (mm^2) Wire Range	Drahtcrimp/Wirecrimp		Isocrimp	Iso.-Ø Ins. Range	Betriebsanl. Instr. Sheet
		Hoehe/Height	Breite/Width	Breite/Width		
967713 / 967719 / 968872	0.5	1.18	2.03	2.54	1.4-1.6	411-18167
	0.75	1.27			1.7-1.9	
	1.0	1.36			1.9-2.1	



539722-2	1	1-539787-4	locator ass.	Positioniereinheit	A
	1	1-539786-3	contact guide	Kontaktabstuetzung	A
	1	1-519151-3	screw M4x25	Schraube M4x25	A
	1	1-519151-2	screw M4x20	Schraube M4x20	A
	1	0-519024-2	hex nut M4	Mutter M4 DIN 985	A
	1	0-519021-8	hex nut M4	Mutter M4 DIN 934	A
	QTY Stck	PN	Description	Benennung	REV

DIMENSIONS: mm-DIN 7168-m		DWN M.Weberndoerfer 18NOV99	MATERIAL -		FINISH -			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		CHK U.Reuter 18NOV99	AMP tyco Electronics AMP GmbH D - 64625 Bensheim					
		APVD -						
		PRODUCT SPEC -	NAME ERGOCRIMP Die Set for MCP 2.8 mm and 2.8 mm Sensor-Flattype Rec.					
		APPLICATION SPEC -						
		WEIGHT -	SIZE A4	CAGE CODE 00779	DRAWING NO C=539722-2	RESTRICTED TO -		
		CUSTOMER DRAWING		SCALE 2:1	SHEET 1	OF 1		
				REV A				