








Max. Temperature: 260° during 10 seconds.

0955 355 3621 741	1	M3	Black insulator	Reel Packaging: 140 connectors (See details on page2/2)			
0955 355 3622 741	1	4-40 UNC					
0955 355 6621 741	2	M3					
0955 355 6622 741	2	4-40 UNC					
0955 355 7621 741	3	M3					
0955 355 7622 741	3	4-40 UNC					
Part number	PL	Screw lock	Index designation				
 All Dimensions in mm Original Size DIN A 3			Techn. Character.		Free size tolerances		
				Dat.	Name	Scale 2 : 1	D-Sub SMT, 25 poles Female, Straight with screw locks and ground pins
			Detail.	25-Oct-11	Johnson.S		
			Insp.	17-Nov-11	Steven.W		
			Stand.	17-Nov-11	Steven.W		
			Zhuhai HARTING Limited 			TB 09 55 355 x62x	Page 1 / 2
EC04070	17-Nov-11	Johnson.S	Sub.				
Mod.	Dat.	Name					



Detail A



See TB 09 55 355 x62x folio 1/2
for connector dimensions
and PCB layout

Packaging in accordance with
EIA 481-2.

0955 355 3621 741	1	M3	Black insulator	Reel Packaging: 140 connectors
0955 355 3622 741	1	4-40 UNC		
0955 355 6621 741	2	M3		
0955 355 6622 741	2	4-40 UNC		
0955 355 7621 741	3	M3		
0955 355 7622 741	3	4-40 UNC		
Part number	PL	Screw lock	Index designation	

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances		