



 HARNESSING

CABLE BRAIDS



✓ Active

 **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE) RAY-101-12.5(10)

RAY-101-12.5(10)
TE Internal Number: CQ50333001

[Always EU RoHS/ELV Compliant](#)

Product Type **Braid**

Plating **Tin**

Braid Material **Copper**

Braid Coverage (%) **93%**

Product Drawings

[Customer Drawing](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



Product Type Features	Product Type	Braid
Electrical Characteristics	DC Resistance (Nominal) (mΩ)	3.23
Body Features	Plating	Tin
	Braid Material	Copper
Dimensions	Length (m)	10
	Length (ft)	32.8
	Weight (Nominal) (kg/km)	65
Usage Conditions	Operating Temperature Range (°C)	-65 – 150
Packaging Features	Packaging Method	Bag

Other	Braid Coverage (%)	93%
-------	--------------------	-----

Product Compliance


Statement of Compliance

PDF

VIEW ALL PRODUCT COMPLIANCE

CUSTOMERS ALSO BOUGHT

CABLE BRAIDS




RAY-101-4.0(10)
RAY-101-4.0(10)

Save to List

Find Similar Products

PCB D-SUB CONNECTORS




25 MSFL PLUG RA 318 (SL, FM)
747238-6

Save to List

Find Similar Products

SURFACE MOUNT RESISTORS




TLR 1206 1.0W R002 1% 50PPM 2K RL
TLR2B10DR002FTDG

Save to List

Find Similar Products

THROUGH-HOLE RESISTORS



ER74 4R7 5% AMMO PK
ER744R7JT

Save to List

Find Similar Products