

BWVT006060201R5M00

Search by : Part Number Characteristics Cross reference

MP

Closed Magnetic Circuit Type - Automatic Assembly

Series Pdf

RoHSREACHCoC

ICP Report

Product detail	
L(mm) ±	6.0±0.20
W(mm) ±	6.0±0.20
T(mm) ±	2.0±0.2
Inductance(uH)	1.5
Tolerance(±%)	20
Test Frequency	100kHz,1V
RDC(ohm)	0.026
RDC Tolerance(±%)	30
Isat(A)Typ	5.4
Isat(A)Max	4.86
Irms(A)Typ	3.7
Irms(A)Max	3.33
Operating Temperature	－55℃～125℃(Including self - temperature rise)

Downloaded from Arrow.com.



Products

Power Inductor

EMI-Common Mode Choke

EMI-Bead

RF-Signal Inductor

RF-Passives/Antennas

LAN Transformer

Resistor & Current Sensor

Applications

Automotive

Industrial

Server/DataCenter

Communication

Mobile and Tablet

Computer/Laptop

Consumer

Design Tools

Simulation Tool

Product Search Engine

E-Catalogue

About Us

Corporate Overview

Corporate Milestones

Core Technology

Certificates & Awards

Quality and Social Responsibility

Investor

Downloaded from Arrow.com.

Financial Information

Corporate governance

Stakeholder Contacts

News

Media Center

New Products

Events

Product Notices

Contact Us

Contact Info

Contact Form

Join Chilisin

Terms of Use

Privacy policy

Sitemap

Inductor

Resistor

Powder

Copyrights © 2018. Chilisin. All rights reserved.

Downloaded from Arrow.com.