Part Number : 1600916020
Product Description : MXP120 Backshell, Exit Direction Straight, Flange Size NW 7.5, with Cable Tie Access, 6 Circuits
Series Number : 160091
Status : Active
Product Category : Connector Accessories



Documents and Resources

Drawings

1600916020_sd.pdf

PK-31302-118-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-34900-0001-001.pdf

AS-34900-0001-CH-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	160091
Description	MXP120 Backshell, Exit Direction Straight, Flange Size NW 7.5, with Cable Tie Access, 6 Circuits
Application	Automotive
Component Type	Cover
Product Name	MXP120 Sealed
UPC	889056640701

Physical

Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.397/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Use with Part(s)

Description	Part Number

Downloaded from Arrow.com.

MXP120 Sealed Receptacle Housings	34900

This document was generated on Oct 08, 2026

Downloaded from Arrow.com.