

- Find by Feature
- Browse by Category
- Browse by Application
- Shore

Search →

Enter part number or keyword

- Search Results (0)
- Search Options

No Search Results

Select a product type to narrow your search:

Connector

Results with your selections: --

Family

- ☐ 0.64
- ☐ 040
- ☐ 070
- ☐ 56
- ☐ 59
- ☐ 090
- ☐ 187
- ☐ ACT
- ☐ APEX
- ☐ ATS
- ☐ Apex
- ☐ BTS
- ☐ Bus-Bar
- ☐ CTS
- ☐ Coax
- ☐ DCK
- ☐ DCS-1
- ☐ DCS-2
- ☐ DS
- ☐ DSQ
- ☐ Ducon
- ☐ DuoTwin
- ☐ Fakra
- ☐ Flexible Power
- ☐ Fuse
- ☐ GT
- ☐ GT Flex Beam
- ☐ GTS
- ☐ GTS-2
- ☐ GTS-3
- ☐ HES
- ☐ HPCS
- ☐ HV150
- ☐ High Power
- ☐ High Voltage
- ☐ Hyllok
- ☐ IDC
- ☐ Lamp Socket
- ☐ MCS
- ☐ MTS
- ☐ MTS-8
- ☐ Metri-Pack
- ☐ Micro
- ☐ Micro HVT
- ☐ Micro-Pack
- ☐ Mixed
- ☐ Modupack
- ☐ OCS
- ☐ Pack-Con III
- ☐ Performance Pack
- ☐ Power Pack
- ☐ RCS800
- ☐ RCS990
- ☐ Shield-Pack
- ☐ Sigma
- ☐ Sleeve
- ☐ Sleeve / Pin
- ☐ Squib / Interface-ABX UC
- ☐ Squib / Interface-ABX-3
- ☐ Squib / Interface-AK-1
- ☐ Squib / Interface-AK-2
- ☐ Squib / Interface-AK-2+
- ☐ Squib / Interface-FCI
- ☐ TTS
- ☐ Timer
- ☐ UC
- ☐ USB 2.0
- ☐ USCAR
- ☐ VF
- ☐ Weather Pack
- ☐ ZRT

Search → Clear

Cavities

- ☐ 1
- ☐ 2
- ☐ 2
- ☐ 3
- ☐ 4
- ☐ 5
- ☐ 6
- ☐ 7
- ☐ 7
- ☐ 8
- ☐ 9
- ☐ 10
- ☐ 11
- ☐ 12
- ☐ 13
- ☐ 14
- ☐ 15
- ☐ 16
- ☐ 17
- ☐ 18
- ☐ 19
- ☐ 20
- ☐ 21
- ☐ 22
- ☐ 23
- ☐ 24
- ☐ 25
- ☐ 26
- ☐ 27
- ☐ 28
- ☐ 29
- ☐ 30
- ☐ 31
- ☐ 32
- ☐ 34
- ☐ 35
- ☐ 36
- ☐ 37
- ☐ 38
- ☐ 39
- ☐ 40
- ☐ 41
- ☐ 42
- ☐ 44
- ☐ 45
- ☐ 46
- ☐ 47
- ☐ 48
- ☐ 49
- ☐ 50
- ☐ 52
- ☐ 54
- ☐ 55
- ☐ 56
- ☐ 57
- ☐ 58
- ☐ 59
- ☐ 60
- ☐ 62
- ☐ 63
- ☐ 64
- ☐ 65
- ☐ 66
- ☐ 68
- ☐ 72
- ☐ 73
- ☐ 74
- ☐ 76
- ☐ 78
- ☐ 80
- ☐ 81
- ☐ 82
- ☐ 84
- ☐ 90
- ☐ 96
- ☐ 100
- ☐ 108
- ☐ 112
- ☐ 116
- ☐ 120
- ☐ 130
- ☐ 133
- ☐ 154
- ☐ 162
- ☐ 169
- ☐ 202

Search → Clear

Gender

- ☐ Female
- ☐ Female + Female
- ☐ Male
- ☐ Male + Female
- ☐ Male + Male

Search → Clear

Sealed

- ☐ Sealed
- ☐ Unsealed

Search → Clear

Terminal(s) blade size [mm]

- ☐ Mixed - Results will have exactly your selections in the same connector.
- ☐ 0.50
- ☐ 0.64
- ☐ 0.8
- ☐ 1.0
- ☐ 1.0 (round)
- ☐ 1.2
- ☐ 1.5
- ☐ 1.8
- ☐ 2.0 (round)
- ☐ 2.3
- ☐ 2.5
- ☐ 2.6
- ☐ 2.8
- ☐ 4.1
- ☐ 4.8
- ☐ 5.7
- ☐ 6.3
- ☐ 8.0
- ☐ 9.5
- ☐ 10.0
- ☐ 20.0

Search → Clear

Product Segment

- ☐ Headers
- ☐ High Power
- ☐ Safety Restraint Systems (SRS)
- ☐ Standard Automotive

Search → Clear


Application

- ☐ A/C Compressor
- ☐ Actuator
- ☐ Aerial / Antenna
- ☐ Airbag
- ☐ Alternator
- ☐ Antenna - Keyless System
- ☐ CAN
- ☐ Camera
- ☐ Cigar Lighter / Power Outlet
- ☐ Diagnostic
- ☐ Door To Body
- ☐ Electrovalve - Cold Start
- ☐ Fan - Engine Cooling
- ☐ Harness - Roof
- ☐ Heater - Rear Window
- ☐ Horn
- ☐ Ignition Coil
- ☐ Immobilizer
- ☐ Injector
- ☐ Inliner
- ☐ Instrument Cluster
- ☐ Lamp - Interior Lamp
- ☐ Lamp - Socket
- ☐ Latch
- ☐ Mirror
- ☐ Module - ABS
- ☐ Module - Airbag
- ☐ Module - Engine
- ☐ Module - Exterior
- ☐ Module - Interior
- ☐ Module - Transmission
- ☐ Motor - Blower
- ☐ Motor - Seat
- ☐ Motor - Wiper
- ☐ Multimedia
- ☐ Pad - Heated Seat
- ☐ Pump
- ☐ Relay
- ☐ Sensor - Accessories
- ☐ Sensor - Brakes
- ☐ Sensor - Crash
- ☐ Sensor - Engine
- ☐ Sensor - Exhaust
- ☐ Sensor - Exterior
- ☐ Sensor - Interior
- ☐ Sensor - Transmission
- ☐ Socket - Multimedia
- ☐ Socket - Tow Bar
- ☐ Speaker
- ☐ Starter
- ☐ Switch
- ☐ Switch - Multifunction

Search → Clear

Clear Search →

2 Way Black 56 Series Unsealed Female Connector



Part #02973872

Question about this product?

- Attributes
- Documents (2)
- Related Products (59)

Part #:	02973872
Description:	2 Way Black 56 Series Unsealed Female Connector
Product Type:	Connector
Status:	Active
Family:	56
Cavities:	2
Terminal(s) blade size [mm]:	6.3
Sealed:	Unsealed
Gender:	Female
Material:	PA66 HI
Weight [g]:	2.08
Color:	Black
ELV compliant:	Yes
RoHS compliant:	Yes
Application:	Lamp - License Plate

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.