Part Number : 1300980116
Product Description : MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, 90° Angle Male, Cable Diameter 14.27-17.45mm (.562-.687")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Part Number : 5541



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, 90° Angle Male, Cable Diameter 14.27-17.45mm (.562-.687")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872165

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	14.27-17.45mm (.562-.687")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	1.000/g
Number of Holes	1
O-Ring	No
Thread Size	3/4" NPT

Mates With / Use With

Downloaded from Arrow.com.

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	1300990144
MAX-LOC Gasket Sealing Ring, 3/4" NPT, Black	1300990150
MAX-LOC O-Ring, 3/4" NPT	1301800333

Downloaded from Arrow.com.