



By Burndy
Catalog # C8

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube,
10 - 2 AWG, 4-1/2" - 6" Water Pipe

Features

- Connects grounding conductor to water pipe or copper tube
- Supplied with Zinc-plated steel hardware

Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe
Or Copper Tube

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
UL Listed	Yes
Certification - UL Listed Direct Burial	N
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Pipe EMT Size	4 in
Conductor - Armored Cable Size	N



Conductor - Pipe EMT Size Range	4 in
Conductor - Rebar Size Range	N/A
Conductor - Copper Str Size Range	10 AWG - 2 AWG

Dimensions

Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm
Dimension - Pad Width inch	1.88 in
Dimension - Height inch	4.29 in
Dimension - Height mm	109 mm
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - Thread Size	-

General

Sub Brand	CLAMP
Material - Hardware	DURIUM™ Silicon Bronze
Trade Name	N
Type	Ground Clamp
UPC 12 Digit	781810142332
UPC 14 Digit GTIN	00781810142332
Material	Bronze Alloy
UPC	781810142332

Logistics

Minimum Pack Quantity	1
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)