

## Specification Sheet

Part Number: 133-01497



Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

|                |           |
|----------------|-----------|
| Article Number | 133-01497 |
|----------------|-----------|

|      |          |
|------|----------|
| Type | SOC14FT6 |
|------|----------|

|       |              |
|-------|--------------|
| Color | Natural (NA) |
|-------|--------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                     |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing. |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                                                 |
|-------------------|-------------------------------------------------------------------------------------------------|
| Short Description | Standoff Bundling Clip, 1.73" Long, Panel Thickness 0.02–0.27", PA66HIRHS, Natural, 2000/carton |
|-------------------|-------------------------------------------------------------------------------------------------|

|                  |                       |
|------------------|-----------------------|
| Global Part Name | SOC14FT6-PA66HIRHS-NA |
|------------------|-----------------------|

|                     |      |
|---------------------|------|
| Length L (Imperial) | 1.77 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Length L (Metric) | 45.0 |
|-------------------|------|

|                          |      |
|--------------------------|------|
| Offset Length (Imperial) | 0.80 |
|--------------------------|------|

|                        |      |
|------------------------|------|
| Offset Length (Metric) | 20.3 |
|------------------------|------|

|                 |          |
|-----------------|----------|
| Fixation Method | Fir Tree |
|-----------------|----------|

|                                |      |
|--------------------------------|------|
| Panel Thickness Min (Imperial) | 0.02 |
|--------------------------------|------|

|                                |      |
|--------------------------------|------|
| Panel Thickness Max (Imperial) | 0.24 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Panel Thickness Min (Metric) | 0.6 |
|------------------------------|-----|

|                              |     |
|------------------------------|-----|
| Panel Thickness Max (Metric) | 6.0 |
|------------------------------|-----|

|                                     |               |
|-------------------------------------|---------------|
| Mounting Hole Diameter D (Imperial) | 0.24 - 0.27 " |
|-------------------------------------|---------------|

|                                   |              |
|-----------------------------------|--------------|
| Mounting Hole Diameter D (Metric) | 6.1 - 6.9 mm |
|-----------------------------------|--------------|

|                                         |      |
|-----------------------------------------|------|
| Mounting Hole Diameter D Min (Imperial) | 0.24 |
|-----------------------------------------|------|

|                                         |      |
|-----------------------------------------|------|
| Mounting Hole Diameter D Max (Imperial) | 0.27 |
|-----------------------------------------|------|

|                                       |     |
|---------------------------------------|-----|
| Mounting Hole Diameter D Max (Metric) | 6.9 |
|---------------------------------------|-----|

|                              |                                                                  |
|------------------------------|------------------------------------------------------------------|
| Material                     | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Material Shortcut            | PA66HIRHS                                                        |
| Flammability                 | UL 94 HB                                                         |
| UV Resistant (Yes/No)        | No                                                               |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)                                |
| Reach Compliant (Article 33) | Yes                                                              |
| ROHS Compliant               | Yes                                                              |
| Package Quantity (Imperial)  | 2000                                                             |
| Package Quantity (Metric)    | 2000                                                             |
| Customs Number               | 3926909988                                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
 Contact Us    RoHS/WEEE Compliance    Disclaimer    Terms and Conditions