






NOTE 1. CONTACT PLATING
CONTACT AREA: GOLD 0.2μm MIN.
TERMINATION AREA: GOLD
ALL OVER NICKEL PLATING



X-X SECTION (5/1)







PART No.	Applicable Wire Size	
PCR-E( )FN+	#26AWG (1/0.4) Discrete Wire Housing Ø0.8~Ø1.0	FN:50pos. only
PCR-E( )FK+	#30AWG (7/0.1) Discrete Wire Housing Ø0.65~Ø0.8	
PCR-E( )FJ+	#28AWG (7/0.127) #30AWG (1/0.254) Discrete Wire Housing Ø0.65~Ø0.8	
PCR-E( )FH+	#32AWG (7/0.08) Discrete Wire Housing Ø0.35~Ø0.5	FH:68pos. only
PCR-E( )FD+	#30AWG (7/0.1) Cohesion Coble	
PCR-E( )FC+	#28AWG (7/0.127) #30AWG (1/0.254) Cohesion Coble	
PCR-E( )FB+	#30AWG (7/0.1) Discrete Wire Housing Ø0.5~Ø0.65	
PCR-E( )FA+	#28AWG (7/0.127) #30AWG (1/0.254) Discrete Wire Housing Ø0.5~Ø0.65	
PCR-E( )F+	#28AWG (7/0.127) #30AWG (1/0.254) Discrete Wire Housing Ø0.8~Ø1.0	

PART. No.	No. OF Pos.	A	B	C	D	CONTACT Pos.# MARKING
		DIMMENSION				
PCR-E96F( )+	96	69.9	61.61	1.27x(48-1)=59.69	64.51	1, 48.49, 96
PCR-E80F( )+	80	59.7	51.45	1.27x(40-1)=49.53	54.35	1, 40, 41, 80
PCR-E68F( )+	68	52.1	43.83	1.27x(34-1)=41.91	46.73	1, 34, 35, 68
PCR-E50F( )+	50	40.7	32.4	1.27x(25-1)=30.48	35.3	1, 25.26, 50
PCR-E36F( )+	36	31.8	23.51	1.27x(18-1)=21.59	26.41	1, 18, 19, 36
PCR-E28F( )+	28	26.7	18.43	1.27x(14-1)=16.51	21.33	1, 14, 15, 28
PCR-E20F( )+	20	21.65	13.35	1.27x(10-1)=11.43	16.25	1, 13, 14, 20

No.	PART NAME	MATERIAL	QTY	FINISH	NOTE
5	CABLE HOUSING	PBT (GF)	2	———	UL94V-0 BLACK
4	SPEACER	PBT (GF)	2	———	UL94V-0 BLACK
3	SHELL	STEEL	1	NICKEL PLATED	———
2	INSULATOR	PBT (GF)	1	———	UL94V-0 BLACK
1	CONTACT	PHOSPHOR BRONZE	No. OF POS.	SEE NOTE 1	———

LTR.	DATE	BY	REV. DESCRIPT
3			
2			
1			

年月日 DATE	尺度 SCALE	単位 UNIT	3角法
MAR.31 (2004)	2/1	mm (INCH)	3RD. A. P

製図 DR.	設計 DE.	検図 CHK.	検図 CHK.	承認 APP.
T. KAWANO	T. KAWANO	T. SOGO	K. HOMMA	S. FURUSAWA

本多通信工業株式会社
HONDA TSUSHIN KOGYO CO., LTD.

名称 NAME	1.27mm SPACING PCR-E TYPE IDC FEMALE CONNCTOR (RoHS)
製番 PART NO.	PCR-E( )F( )+

ID= PCR-E@F@+ E0

HONDA TSUSHIN KOGYO CO., LTD.
This product information in this data is for reference only. Please request the Engineering Drawing for the most current and accurate product information. Contact our sales staff for further information before considering any of our products. Specifications subject to change without notice.

Downloaded from Arrow.com.