

Home Inspector Kit

Specifically designed for home inspection professionals

Aids in identification of moisture, HVAC, electrical and hot water system issues.

A \$67 in savings when purchased as a kit!

Kit includes:

- Model MO280 Pinless moisture meter
 - Select from 10 different wood types
 - Displays %moisture from 0 to 99%
 - Measurement depth to 0.75" (22mm) below the surface
- Model 42500 Mini IR Thermometer
 - Ideal for testing HVAC supply and return applications
 - Measures from -4 to 500°F (-20 to 260°C)
 - Built-in laser pointer improves aim and identifies target
 - 0.95 fixed emissivity with 6:1 distance to target ratio
- Model ET10 GFCI Receptacle Tester
 - Tests for faulty wiring in 3-wire receptacles and GFCI Circuits
 - Detects 5 wiring faults
 - Lights indicate circuit condition
- Model 39240 Waterproof Stem Thermometer
 - Ideal for testing hot water heaters
 - Measures from -40 to 392°F (-40 to 200°C)
 - 2.75" (70mm) stainless steel stem
- Supplied in an attractive storage case that provides protection and organization for the testers whenever they are needed



Measure moisture of wall material with non-invasive Pinless technology

Ordering Information:

MO280-KHHome Inspector Kit



www.extech.com

Specifications subject to change without notice.

Copyright © 2007-2008 Extech Instruments Corporation. All rights reserved including the right of reproduction in whole or in part in any form.

6/19/08 - R1