

This document was generated on 03/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [**1301110027**](#)

Status: **Active**

Overview:

Description: Safety Yellow Molded Stringlight, 200W, 14/2 SJTW with 2.43m Lead, 10 Sockets with Guards, Lamp-It-In-the-Box Packaging, Overall Length 30.48m (100.0')

Agency Certification

UL

E112216

General

Product Family
Series

NEMA Configuration

NEMA Rating

Outlet

Overview

Product Name

Type

UPC

Portable Lighting

[130111](#)

NEMA 1-15

Rain Tight

None

stringlights

Safety Yellow

String Lights

78678840867

Physical

Cord Length - Primary

2.43m (8.0')

Cord Length - Secondary

0.61m (2.0')

Depth

N/A

Duty

Commercial

Guard Included

Yes

Guard Type

Polypropylene

Height

N/A

Length

30.48m (100.0')

Material - Guard

Polypropylene

Mounting Style

Stringer

Packaging Type

Carton

Socket Construction

Molded

Electrical

Bulb Type

Incandescent

Cord Type - Primary

14/2 SJTW

Lamp Type

A21

Lamp Wattage - Maximum

200W

Lumens

2000

On/Off Switch

No

Voltage (Fixture) - Maximum

120VAC 60 HZ

Material Info

Engineering Number

5000

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130111 Series](#)

This document was generated on 03/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION