



Part Number : [1061141200](#)
Product Description : EMI MPO Adapter, Simplex,
Metal Body, Snap Mount Style, Shutter, Foam Gasket
Series Number : 106114
Status : Active
Product Category : Fiber Optic Adapters
Engineering Number : 861141200




Documents & Resources

Drawings

[1061141200_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Adapters
Series	106114
Description	EMI MPO Adapter, Simplex, Metal Body, Snap Mount Style, Shutter, Foam Gasket
Component Type	EMI Shielding
Product Name	MPO
Type	Adapter
UPC	822350276801

Electrical

Shielded	Yes
Shield Type	EMI Gasket

Physical

Alignment Sleeve	N/A
Angled Physical Contact (APC)	N/A
Color - Resin	N/A
Gender	Female-Female
Material - Housing	Die-Cast
Mounting Style	Snap
Net Weight	10.718/g
Orientation	Straight
Panel Mount	With Flange
Ports	1
Shutter	One Side

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Jul 10, 2025