


PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
C2**2 (SEE NOTE 1)	78.74 IN $\pm$.18 IN (2000.0mm $\pm$ 4.6mm)	0.72 LB (327g)	0.11 LB/FT (1.6g/cm)
C2**6 (SEE NOTE 1)	72.00 IN $\pm$.18 IN (1828.8mm $\pm$ 4.6mm)	0.66 LB (299g)	0.11 LB/FT (1.6g/cm)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D35245CM_DC_C2_00.prt

CAD FILENAME/LAYERS

C2.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS

FIBER-DUCT 2x2 COVER
(C2**2, C2**6)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) $\pm$ (.XXX) $\pm$
(.XX) $\pm$.03 (0.8) ANGLES $\pm$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

MAT'L:

SCALE

NONE

DATE

1-5-07

PVC

DRAWING NO.

35245-39

DWG

A

CHK'D

RN

SIZE

R	1-5-07	MSO	RN	RELEASED TO PRODUCTION	35245-39	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH