




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/25/20	
A		ADDED SPEC.	5/19/21	LH/RC



SW-PB1-1XX-A-P1-X	
NO.	Button Color
A	Black
B	Blue
C	Green
D	Red
E	White
F	Yellow

SPECIFICATIONS:

Material:
Housing: ABS, rated UL 94V-0
Bottom: PA66
Button: ABS
Contact: Brass, Silver plated
Spring: Spring steel wire
Electrical:
Rating: 3A, 250VAC
Contact resistance: 50 m Ω max
Insulation resistance: 100 Mohms min (500VDC)
Dielectric withstanding voltage: 1500 VAC for 1 minute
Electrical life: 10,000 Cycles min
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X $\pm$.10	ϕ .X $\pm$.10
.XX $\pm$.020	ϕ .XX $\pm$.015
.XXX $\pm$.015	ϕ .XXX $\pm$.010

DRAWN	OW	11/25/20
CHECKED	AC	11/25/20
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

SW-PB1-1XX-A-P1-X

DZ= ON-OFF Latching
BS= OFF-ON Momentary

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
SWITCH, PLASTIC PUSH BUTTON, SPST
SOLDER TYPE

SIZE	PART NO.	REV.
X	SW-PB1-1XX-A-P1-X	-
REF:	S00204C	SCALE: NTS
SHEET 1 OF 1		