

NOTES:

1.ENVIRONMENTAL: TEMPERATURE RANGE -20° TO +85°.

2.ELECTRICAL:

RATED: 1.5A @ 40V AC (ms)

CONTACT RESISTANCE: 20 MILLIOHMS MAXIMUM

INSULATION RESISTANCE: 1000 MEGOHMS MINIMUM

DIELECTRIC WITHSTANDING VOLTAGE:500V AC (ms)

3.MECHANICAL:

MATING FORCE: 10 LB.(4.5Kg) MAXIMUM

UNMATING FORCE: 2.2LB.(1Kg) MINIMUM,8.8LB.(4Kg)MAXIMUM


4.MATERIAL:

HOUSING: GLASS FILLED THERMOPLASTIC,NATURAL,UL 94V-0




CONTACT: PHOSPHOR BRONZE

SHELL :NICKELOVER CU PLATED

BOARD LOCK : ZINC ALLOY,TIN PLATED



RECOMMENDED P.C.B LAYOUT
TOLERANCES: ±0.05mm



UNLESS OTHERWISE
SPECIFIED TOLERANCE

ANG.	±J°
.0	±0.30
.00	±0.20

RoHS
Compliant

ITEM NO

A-DVI-D-R

TITLE

DVI Connector integrated 24+5
Socket right angle type

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283

Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED

© Copyright 2008 by Assmann Electronic Components
All International Rights Reserved