Part Number : 936014688
Product Description : Heavy-Duty Standard (STD) Single Lever Coupler, Polyamide, with 1 Lever, Top Entry, with Cable Gland, Size «32x13», Pg16 Thread, Black
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7908.6667.1



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Single Lever Coupler, Polyamide, with 1 Lever, Top Entry, with Cable Gland, Size «32x13», Pg16 Thread, Black
Component Type	Single Lever Coupler
IP Rating	IP66, IP67
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191842691

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V

Physical

Cable Diameter	8.00-14.00mm
Component Size	«32X13»
Entry Location	Top
Flammability	UL 94V-0
Gland Color	Black RAL 9005
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Hood	Polyamide
Material - Lever	Polyamide

Downloaded from Arrow.com.

Net Weight	41.800/g
Number of Levers	1
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size «32x13» S-QD Inserts

Downloaded from Arrow.com.